



## BE18G98

by Burndy  
Catalog ID: BE18G98

Flexible Copper Braid

## Product Details

### General

|                                       |              |
|---------------------------------------|--------------|
| Connector Type                        | Braid        |
| Material                              | Copper       |
| Material - Ferrules                   | Y            |
| Physical Attribute - Number of Braids | 1            |
| Plated                                | Y            |
| UPC                                   | 621945471481 |
| UPC 12 Digit                          | 0            |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 457 mm   |
| Dimension - Length Overall inch | 18.00 in |

### Certifications and Compliance

|   |       |
|---|-------|
| Certification - CSA Approved            | No    |
| Certification - ETL                     | No    |
| Certification - UL Listed Direct Burial | No    |
| Certification - UL Recognized           | No    |
| Certification - cULus                   | No    |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | EX    |
| UL Listed                               | No    |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)