



## BE37D50G42

by Burndy  
Catalog ID: BE37D50G42

Flexible Copper Braid

### Product Details

#### General

|                                       |               |
|---------------------------------------|---------------|
| Connector Type                        | Braid         |
| Material                              | Copper        |
| Material - Ferrules                   | Y             |
| Physical Attribute - Number of Braids | 1             |
| Plated                                | Y             |
| UPC                                   | 781810442432  |
| UPC 12 Digit                          | 7818104424322 |

#### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 953 mm   |
| Dimension - Length Overall inch | 37.50 in |

#### Electrical Ratings

|                           |     |
|---------------------------|-----|
| Rating - Indoor Amperage  | 340 |
| Rating - Outdoor Amperage | 405 |

#### Certifications and Compliance

|   |       |
|---|-------|
| Certification - CSA Approved            | Yes   |
| Certification - ETL                     | No    |
| Certification - UL Listed Direct Burial | No    |
| Certification - UL Recognized           | No    |
| Certification - cULus                   | No    |
| Industry Standard(s)                    | UL467 |
| Standards - Industry Standards Met      | UL467 |
| Standards - RoHS Compliance Status      | NC    |
| UL Listed                               | Yes   |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)