



BE7D50G91W

by Burndy
Catalog ID: BE7D50G91W

Tin Plated Ferrules

Product Details

General

| | |
|----------------|---------------|
| Connector Type | Braid |
| Material | Copper |
| UPC | 781810205341 |
| UPC 12 Digit | 7818102053411 |

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)