



BF12N

by Burndy
Catalog ID: BF12N

FLEXIBLE COPPER BRAID.

Product Details

General

| | |
|---------------------------------------|---------------|
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 1 |
| Plated | Y |
| UPC | 781810004883 |
| UPC 12 Digit | 7818100048833 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - D inch | 3.00 in |
| Dimension - Hole Size inch | 0.56 in |
| Dimension - L Length Overall mm | 305 mm |
| Dimension - Length Overall inch | 12.00 in |
| Dimension - N inch | 0.62 in |
| Dimension - Pad Width inch | 1.19 in |

Electrical Ratings

| | |
|---------------------------|-----|
| Rating - Indoor Amperage | 360 |
| Rating - Outdoor Amperage | 430 |

Certifications and Compliance

| | |
|---|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |

| | |
|------------------------------------|-------|
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)