



BF33D50G87TN

by Burndy
Catalog ID: BF33D50G87TN

Tin Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
UPC	781810537909
UPC 12 Digit	7818105379099

Dimensions

Dimension - D inch	1.50 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	851 mm
Dimension - Length Overall inch	33.50 in
Dimension - N inch	0.75 in
Dimension - Pad Width inch	1.19 in

Electrical Ratings

Rating - Indoor Amperage	360 A
Rating - Outdoor Amperage	430 A

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	UI
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)