



BF36N1

by Burndy
Catalog ID: BF36N1

Flexible Copper Braid

Product Details

General

Connector Type	Braid
Material	Copper
UPC	781810538166
UPC 12 Digit	7818105381666

Dimensions

Dimension - D inch	1.25 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	914 mm
Dimension - Length Overall inch	36 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.19 in

Electrical Ratings

Rating - Indoor Amperage	360 A
Rating - Outdoor Amperage	430 A

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity

100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)