



## BG19N

by Burndy  
Catalog ID: BG19N

Flexible Copper Braid

## Product Details

### General

|                |               |
|----------------|---------------|
| Connector Type | Braid         |
| Material       | Copper        |
| UPC            | 781810550953  |
| UPC 12 Digit   | 7818105509533 |

### Dimensions

|                                 |          |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 483 mm   |
| Dimension - Length Overall inch | 19.00 in |

### Electrical Ratings

|                           |       |
|---------------------------|-------|
| Rating - Indoor Amperage  | 415 A |
| Rating - Outdoor Amperage | 495 A |

### Certifications and Compliance

|                                    |       |
|------------------------------------|-------|
| Certification - CSA Approved       | No    |
| Certification - ETL                | No    |
| Certification - UL Recognized      | No    |
| Certification - cULus              | No    |
| Industry Standard(s)               | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM    |
| UL Listed                          | Yes   |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)