



BG22N

by Burndy
Catalog ID: BG22N

Flexible Copper Braid

Product Details

General

| | |
|----------------|---------------|
| Connector Type | Braid |
| Material | Copper |
| UPC | 781810550939 |
| UPC 12 Digit | 7818105509399 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 559 mm |
| Dimension - Length Overall inch | 22.00 in |

Electrical Ratings

| | |
|---------------------------|-------|
| Rating - Indoor Amperage | 415 A |
| Rating - Outdoor Amperage | 495 A |

Certifications and Compliance

| | |
|------------------------------------|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)