



BG25N

by Burndy
Catalog ID: BG25N

Prop 65 Notice

Flexible Copper Braid

Product Details

General

Connector Type	Braid
Material	Copper
UPC	781810370704
UPC 12 Digit	7818103707044

Dimensions

Dimension - L Length Overall mm	635 mm
Dimension - Length Overall inch	25.00 in

Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)