



## BG288N

by Burndy  
Catalog ID: BG288N

Flexible Copper Braid

## Product Details

### General

Connector Type	Braid
Material	Copper
UPC	781810200100
UPC 12 Digit	7818102001000

### Dimensions

Dimension - L Length Overall mm	7315 mm
Dimension - Length Overall inch	288.00 in

### Electrical Ratings

Rating - Indoor Amperage	415 A
Rating - Outdoor Amperage	495 A

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)