

# BGBL4RK

by Burndy  
Catalog ID: BGBL4RK

Prop 65 Notice

High Strength AL6061-T6 Aluminum Lay-In Lug, Conductor Range (Main/Primary): 14 - 1/0 AWG, Voltage Rating: 600 V, Bolt Size: 1/4-28.

Features: The Lay-In QIKLUG, Type BGBL Is Manufactured From High Strength 6061-T6 Aluminum, And Is Ideally Suited For Grounding And Bonding Applications Accommodating Both Copper And Aluminum Conductor Sizes #14 AWG To 250 KCMIL, UL486B Listed, AL9CU Rated, For Copper And Aluminum Conductor Combinations Up To 90 DEG C, 600 V Applications, UL Recognized For Grounding And Bonding. Ensures Reliability, Electro-Tin Plated, Provides Low Contact Resistance, Lay-In Feature, Eases Installation, Width: 0.39 IN Pad, Dimension D: 0.62 IN, Length: 1.1 IN, Height: 0.78 IN, Installation Torque: 35 IN-LB, Set Screw Type: Slot, Thickness: 0.13 IN, Package: Clamshell, Dimension T: 0.13 IN, Dimension N: 0.2 IN, Conductor Type: Copper, Aluminium



## Product Details

### General

Application	For Grounding And Bonding Applications
Sub Brand	QIKLUG
Trade Name	QIKLUG™
Type	BGBL
UPC	781810359648
UPC 12 Digit	7818103596488

### Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	10
Number of Pieces in Package	3

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)