

BGBL4SS

by Burndy
Catalog ID: BGBL4SS

Prop 65 Notice

WIRE: #4-14 AL/CU AL9CU; STUD: #10 RECOMMENDED TORQUE: #4-6 AWG 35 LB-IN #8 AWG 25 LB-IN #10-14 AWG 20 LB-IN; Stainless Steel Hardware.



Product Details

General

Hardware Type	1/4-18 UNF-2B
Hex Size	Slot
Installation Torque Recommended in-lb	35 Lb-in
Material	Aluminum
Material - Hardware	Stainless Steel
Material Type - Screw	Steel - Zinc Plated
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Slot
Plated	Y
Plating Type	Tin
Temperature Rating	194
Trade Name	QIKLUG™
UPC	781810478745
UPC 12 Digit	7818104787455

Dimensions

Dimension - D inch	0.62 in
Dimension - Height fraction	4/5 in
Dimension - Height inch	.78 in
Dimension - Hole Size inch	0.22 in
Dimension - Hole Size mm	6 mm
Dimension - L Length Overall mm	27 mm
Dimension - Length Overall inch	1.07 in
Dimension - N inch	0.19 in
Dimension - Pad Width inch	0.39 in
Dimension - Width fraction	3/8 in
Dimension - Width inch	0.38 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size	8 AWG;6 AWG;4 AWG
Conductor - AL Str Size Range	8 AWG-4 AWG
Conductor - Copper Solid Size	14 AWG;13 AWG;12 AWG;11 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	14 AWG-4 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	14 AWG-4 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Size• CU C Str-Size• CU C Solid-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-B
Standards - Industry Standards Met	UL 486A-B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	2400 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)