



BIBD6004MT

by Burndy
Catalog ID: BIBD6004MT

Prop 65 Notice

Aluminum Multiple Tap Connector w/ Mount Holes, Clear Insulated, 4 Port, 2 Sided Entry, 4 AWG-600 kcmil, Al/Cu Rated.

Features: The BIBD-MT Series UNITAP Offer The Same Multi-Port Capabilities As The Standard UNITAP Connectors Except These -MT Types Are Provided With Two Isolated Mounting Holes At Both Ends Of The Connector For Direct Mounting To A Trough, Gutter Or Wireway, They Will Accommodate Up To Standard 1/4 IN Hardware, Conductor Size (run - Range): 4 AWG - 600 KCMIL, Hex Size (key): 3/8 IN, Wire Entry: Double, Number Of Ports: 4

Product Details

General

Application	For Indoor Use Only, Copper Or Stranded Aluminum, Mountable
Hex Key	3/8
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Material - Hardware	Aluminum
Number Of Ports	4
Physical Attribute - Number of Screws	6
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBD-MT, Multi-Port
UPC	781810253403
UPC 12 Digit	7818102534033

Dimensions

Dimension - Height fraction	2.875 in
Dimension - Height inch	2.88 in
Dimension - L Length Overall mm	199 mm
Dimension - Length Overall inch	7.84 in
Dimension - Width inch	3.00 in
Dimension - Width mm	76 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Size Range	4 AWG-600 kcmil
Conductor - Copper Str Size	4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil
Conductor - Copper Str Size Range	4 AWG-600 kcmil
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)