



## BIBD7504FX

by Burndy  
Catalog ID: BIBD7504FX

Prop 65 Notice

MULTI-PORT Double-Sided Entry.

### Product Details

#### General

Color Code	Black
Insulation	Y
Material	Aluminum
Number Of Ports	4
Plated	Y
Plating Type	Tin
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
UPC	621945439252
UPC 12 Digit	6219454392522

#### Dimensions

Dimension - Length Overall inch	5.375 in
---------------------------------	----------

#### Electrical Ratings

Amperage Rating	475 A
Rating - Minimum Voltage	600

#### Conductor Related

Conductor - AL Str Size Range	2AWG-535 kcmil
Conductor Type	<ul style="list-style-type: none"><li>AL C Str-Size</li><li>CU C Str-Size</li></ul>

#### Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)