

# BIBS2/010FXMT

by Burndy  
Catalog ID: BIBS2/010FXMT

MOUNTING VERSIONMULTI-PORTSingle-Sided Entry.



## Product Details

### General

Color Code	Black
Insulation	Y
Material	Aluminum
Number Of Ports	10
Physical Attribute - Number of Screws	12
Plated	Y
Plating Type	Tin
Temperature Rating	-40° C to 135 °C
Trade Name	UNITAP™
UPC	621945440272
UPC 12 Digit	6219454402722

### Dimensions

Dimension - Length Overall inch	7.986 in
---------------------------------	----------

### Electrical Ratings

Amperage Rating	175 A
Rating - Minimum Voltage	600

### Conductor Related

Conductor - AL Str Size Range	1 AWG-14 AWG
Conductor Type	<ul style="list-style-type: none"> <li>AL C Str-Size</li> <li>CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)