

# BIBS2/08FX

by Burndy  
Catalog ID: BIBS2/08FX

MULTI-PORT Single-Sided Entry.



## Product Details

### General

Color Code	Black
Insulation	Y
Material	Aluminum
Number Of Ports	8
Plated	Y
Plating Type	Tin Plated Aluminum
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945439559
UPC 12 Digit	6219454395599

### Dimensions

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	134.37 mm
Dimension - Length Overall inch	5.298 in
Dimension - Width inch	1.31 in
Dimension - Width mm	33 mm

### Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

### Conductor Related

Conductor - Copper DLO Size Range	14 - 1 Str
Conductor - Copper Flex G Size Range	14 - 1 Str
Conductor - Copper Flex H Size Range	14 - 1 Str
Conductor - Copper Flex I Size Range	14 - 1 Str
Conductor - Copper Flex K Size Range	14 - 1 Str
Conductor - Copper Str Size Range	14 - 2/O Str
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> <li>• CU C Fex-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)