

# BIBS25012FXMT

by Burndy  
Catalog ID: BIBS25012FXMT

MOUNTING VERSIONMULTI-PORTSingle-Sided Entry.



## Product Details

### General

Color Code	Yellow
Insulation	Y
Material	Aluminum
Number Of Ports	12
Plated	Y
Plating Type	Tin Plated Aluminum
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945440333
UPC 12 Digit	6219454403333

### Dimensions

Dimension - Height inch	2.13 in
Dimension - L Length Overall mm	331.22 mm
Dimension - Length Overall inch	13.04 in
Dimension - Width inch	2 in
Dimension - Width mm	51 mm

### Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

### Conductor Related

Conductor - Copper DLO Size Range	10 - 3/0 Str
Conductor - Copper Flex G Size Range	10 - 3/0 Str
Conductor - Copper Flex H Size Range	10 - 3/0 Str
Conductor - Copper Flex I Size Range	10 - 3/0 Str
Conductor - Copper Flex K Size Range	10 - 3/0 Str
Conductor - Copper Str Size Range	10 - 250 Str
Conductor Type	<ul style="list-style-type: none"> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> <li>• CU C Fex-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)