

BIBS2504FX

by Burndy
Catalog ID: BIBS2504FX

Prop 65 Notice

MULTI-PORT Single-Sided Entry.



Product Details

General

Color Code	Yellow
Insulation	Y
Material	Aluminum
Number Of Ports	4
Plated	Y
Plating Type	Tin Plated Aluminum
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945439634
UPC 12 Digit	6219454396344

Dimensions

Dimension - Height inch	2.13 in
Dimension - L Length Overall mm	92.96 mm
Dimension - Length Overall inch	3.66 in
Dimension - Width inch	2.13 in
Dimension - Width mm	54 mm

Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

Conductor Related

Conductor - Copper DLO Size Range	10 - 3/0 Str
Conductor - Copper Flex G Size Range	10 - 3/0 Str
Conductor - Copper Flex H Size Range	10 - 3/0 Str
Conductor - Copper Flex I Size Range	10 - 3/0 Str
Conductor - Copper Flex K Size Range	10 - 3/0 Str
Conductor - Copper Str Size Range	10 - 250 Str
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Fex-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)