



BIBS3505DB

by Burndy
Catalog ID: BIBS3505DB

Prop 65 Notice

Multi Port Direct Burial, 5 Ports, 350 kcmil-12 AWG Str, 600 V.

Dual rated for aluminum or copper conductors, Each unit is individually marked for ease of identification

Product Details

General

Application	For Outside Direct Burial
Installation Torque Recommended in-lb	450 LBS/in
Insulation	Y
Material	Aluminum
Number Of Ports	5
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port - Direct Burial
UPC	781810523612
UPC 12 Digit	7818105236122

Dimensions

Dimension - Height inch	2.46 in
Dimension - L Length Overall mm	158 mm
Dimension - Length Overall inch	6.24 in
Dimension - Strip Length inch	1.125
Dimension - Width inch	4.06 in
Dimension - Width mm	103 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size Range	12 - 350 Str
Conductor - Copper Str Size Range	12 - 350 Str
Conductor Type	<ul style="list-style-type: none"> AL C Str-Size CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)