

BIBS3506FXMT

by Burndy
Catalog ID: BIBS3506FXMT

MOUNTING VERSIONMULTI-PORTSingle-Sided Entry.



Product Details

General

Color Code	Red
Insulation	Y
Material	Aluminum
Number Of Ports	6
Plated	Y
Plating Type	Tin Plated Aluminum
Temperature Rating	135°C
Trade Name	UNITAP™
UPC	621945440401
UPC 12 Digit	6219454404011

Dimensions

Dimension - Height inch	2.5 in
Dimension - L Length Overall mm	188.72 mm
Dimension - Length Overall inch	7.43 in
Dimension - Width inch	2.25 in
Dimension - Width mm	57 mm

Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

Conductor Related

Conductor - Copper DLO Size Range	10 - 250 Str
Conductor - Copper Flex G Size Range	10 - 250 Str
Conductor - Copper Flex H Size Range	10 - 250 Str
Conductor - Copper Flex I Size Range	10 - 250 Str
Conductor - Copper Flex K Size Range	10 - 250 Str
Conductor - Copper Str Size Range	10 - 350 Str
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Fex-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)