



BIBS43FX

by Burndy
Catalog ID: BIBS43FX

Prop 65 Notice

UNITAP, In-Line Splice Reducer, #14-#1/0 Class B & C, #14-#1 ClassG,H,I,K, DLO, Aluminum.

Features: Clear Plastisol covered AL6061-T6 aluminum body, Saves time, lowers installation costs, eliminates taping, Oxide inhibitor pre-installed, Inhibits moisture and contaminants from entering the contact area

Product Details

General

Application	Tap connections and in-line splice/reductions are made quickly and easily with the UNITAP™ line of connectors
Color Code	Brown
Insulation	Y
Material	Aluminum
Number Of Ports	3
Plated	Y
Plating Type	Tin Plated Aluminum
Sub Brand	UNITAP
Temperature Rating	135°C
Trade Name	UNITAP™
Type	BIBS, Multi-Port
UPC	621945439757
UPC 12 Digit	6219454397577

Dimensions

Dimension - Height inch	1.25 in
Dimension - L Length Overall mm	32.26 mm
Dimension - Length Overall inch	1.27 in
Dimension - Width inch	1.13 in
Dimension - Width mm	29 mm

Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

Conductor Related

Conductor - Copper DLO Size Range	14 - 6 Str
Conductor - Copper Flex G Size Range	14 - 6 Str
Conductor - Copper Flex H Size Range	14 - 6 Str
Conductor - Copper Flex I Size Range	14 - 6 Str
Conductor - Copper Flex K Size Range	14 - 6 Str

Conductor - Copper Str Size Range	14 - 4 Str
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Fex-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)