



## BIBS44RK

by Burndy  
Catalog ID: BIBS44RK

Prop 65 Notice

Single Entry, #14 - #4 AWG; 4 Port; Suitable for Hanging on POS Rack.

## Product Details

### General

Hex Key	1/8 in
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	4
Physical Attribute - Number of Screws	4
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Temperature Rating	194
Trade Name	UNITAP™
UPC	781810361665
UPC 12 Digit	7818103616655

### Dimensions

Dimension - Height inch	1.25 in
Dimension - L Length Overall mm	50 mm
Dimension - Length Overall inch	19.95 in
Dimension - Screw Size inch	1/4
Dimension - Width inch	1.25 in
Dimension - Width mm	32 mm

### Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

### Conductor Related

Conductor - AL Str Size Range	14 - 4 Str
Conductor - Copper Str Size Range	14 - 4 Str
Conductor Type	<ul style="list-style-type: none"> <li>AL C Str-Size</li> <li>CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
Number of Pieces in Package	1
Packaging Type	Clamshell

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)