



BIBS5005DB

by Burndy
Catalog ID: BIBS5005DB

Prop 65 Notice

Multi-Port Single Sided Entry, Multi-Port Single Sided Entry, 5, 500 kcmil-12 AWG Str.

Dual rated for aluminum or copper conductors, Each unit is individually marked for ease of identification

Product Details

General

Application	For Outside Direct Burial
Installation Torque Recommended in-lb	550 LBS/in
Insulation	Y
Material	Aluminum
Number Of Ports	5
Plated	N
Plating Type	Unplated
Sub Brand	UNITAP
Temperature Rating	194
Trade Name	UNITAP™
Type	BIBS, Multi-Port - Direct Burial
UPC	781810523650
UPC 12 Digit	7818105236500

Dimensions

Dimension - Height inch	3.13 in
Dimension - L Length Overall mm	179 mm
Dimension - Length Overall inch	7.06 in
Dimension - Strip Length inch	1.50
Dimension - Width inch	4.58 in
Dimension - Width mm	116 mm

Electrical Ratings

Operating Voltage	600 V
Rating - Minimum Voltage	600

Conductor Related

Conductor - AL Str Size Range	12 - 500 Str
Conductor - Copper Str Size Range	12 - 500 Str
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)