



BIT4FX

by Burndy
Catalog ID: BIT4FX

Prop 65 Notice

UNITAP, Tap- Opposite Sided Entry, #14-2/0 Class B & C, #14-#1 Class G,H,I,K, DLO, Aluminum.

Features: Clear Plastisol covered AL6061-T6 aluminum body, Saves time, lowers installation costs, eliminates taping, Oxide inhibitor pre-installed, Inhibits moisture and contaminants from entering the contact area

Product Details

General

Application	Clear Insulated Multiple Tap Connectors
Color Code	Brown
Hex Key	1/8 in
Insulation	Y
Insulation Type	Plastisol
Material	Aluminum
Number Of Ports	2
Plated	Y
Plating Type	Tin Plated
Sub Brand	UNITAP
Temperature Rating	135°C
Trade Name	UNITAP™
Type	BIT, UNITAP
UPC	621945440036
UPC 12 Digit	6219454400366

Dimensions

Dimension - Height inch	1.25 in
Dimension - L Length Overall mm	27.44 mm
Dimension - Length Overall inch	1.08 in
Dimension - Width inch	1.13 in
Dimension - Width mm	28.70 mm

Electrical Ratings

Operating Voltage	600 V
-------------------	-------

Conductor Related

Conductor - AL Str Size Range	14 str.- 4 str.
Conductor - Copper DLO Size Range	14 str.-6 str.
Conductor - Copper Flex G Size Range	14 str.-6 str.
Conductor - Copper Flex H Size Range	14 str.-6 str.

Conductor - Copper Flex I Size Range	14 str.-6 str.
Conductor - Copper Flex K Size Range	14 str.-6 str.
Conductor - Copper Str Size Range	14 str.-4str.
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Size • CU C Str-Size • CU C Flex-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)