



BMYPCHMT

by Burndy
Catalog ID: BMYPCHMT

Prop 65 Notice

Cast Iron Bench Mount, 6.19 IN L, Black Lacquer Coated, For Use on MY28 and MY29 HYTOOL™ Only, Use 3/8" hardware to mount to workbench and 1/4" hardware to mount tool.

- ALTERNATE MATERIAL: ALLOY 30 AND 365-T6 ALUMINUM

Product Details

General

Application - For Use On	For use on MY28 and MY29 HYTOOL™ only
Finish Type	Coated With Black Lacquer
Material	CAST IRON, ALTERNATE MATERIAL: ALLOY 30 AND 365-T6 ALUMINUM
Tool Type	Bench Mount
UPC	781810011171
UPC 12 Digit	7818100111711

Dimensions

Height	2.81 in
Length	6.19 in
Width	3.25 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)