



BSD2050N

by Burndy
Catalog ID: BSD2050N

Prop 65 Notice

Static Discharge Reels, Heavy Duty, Cable Length: 50 Feet (Nylon Covered), Weight: 12 LB.

Number Of Clamping Elements: 1, Tension: Adjustable, Cable Type: Aircraft Steel, Outer Shell Material: Nylon, Cable Lock: Yes, Housing Color: Red

Product Details

General

Application	Used to dissipate static charge build-up developed while filling or dispensing fuel or other combustible liquids from fuel trucks or rail cars
Cable Length	50 ft
Cable Lock	Y
Cable Type	Aircraft Steel
Color - Housing	Red
Material	Copper
Material Type - Outer Shell	Nylon
Physical Attribute - Number of Clamping Elements	1
Plated	N
Plating Type	Unplated
Sub Brand	REEL
Tension	Adjustable
Type	Static Discharge Reel
UPC	781810504475
UPC 12 Digit	7818105044755

Dimensions

Cable Length Active	600
Dimension - Height inch	8.8 in
Dimension - L Length Overall mm	219 mm
Dimension - Length Overall inch	8.6 in
Dimension - Width inch	3.40 in
Dimension - Width mm	86 mm

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)