

BULF18NG

by Burndy
Catalog ID: BULF18NG

Bullet Female Connectors, 18-22 AWG, 0.89" L, 0.16" W, 3 PC Nylon Insul, Red(Insul Color).

Size: 0.157 IN Diameter



Product Details

General

Application	For easier wire insertion
Insulation Type	3 Piece Nylon
Sub Brand	SMALL TERMINAL
Type	Bullet Style
UPC	781810525005

Dimensions

Dimension - B Length inch	0.21 in
Dimension - L Length Overall mm	23 mm
Dimension - Length Overall inch	0.89 in
Dimension - Strip Length inch	5/16 in

Conductor Related

Conductor - Copper Solid Size Range	12 AWG - 10 AWG
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)