



BULF18N

by Burndy
Catalog ID: BULF18N

Bullet Female Connectors, 18-22 AWG, 0.89" L, 0.16" W, Molded Nylon Insul, Red(Insul Color).

Size: 0.157 IN Diameter

Product Details

General

Application	For easier wire insertion
Insulation Type	2 Piece Nylon
Sub Brand	SMALL TERMINAL
Trade Name	HYDENT™
Type	Bullet Style
UPC	781810524992
UPC 12 Digit	7818105249922

Dimensions

Dimension - B Length fraction	0.21 in
Dimension - Strip Length inch	5/16 in

Conductor Related

Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)