

BYNA39RT15HACCC

by Burndy
Catalog ID: BYNA39RT15HACCC

Prop 65 Notice

HYLUG™ Terminal Pad Assembly (ACCC) with TMH24 Hardware Kit, 713 kcmil, 330mm², 380mm² ACCC, 15°, 230kV



Product Details

General

Connector Type	Terminal
Die Index	722
Installation Torque Recommended in-lb	300 in-lb
Material	Aluminum
Trade Name	HYLUG™
UPC	781810474600
UPC 12 Digit	7818104746000

Dimensions

Dimension - D inch	4.50 in
Dimension - Hole Size inch	0.56 in
Dimension - Inside Diameter inch	0.97 in
Dimension - L Length Overall mm	411 mm
Dimension - Length Overall inch	16.2 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Pad Width inch	3.25 in
Physical Attribute - Tongue Angle	15 Degree

Conductor Related

Conductor - ACCC Str Size	713 kcmil(Dove);330mm ² (Oslo);380mm ² (Amsterdam)
---------------------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)