

## BYNA39RT15HT

by Burndy  
Catalog ID: BYNA39RT15HT

BURNDY; HYLUG; BYNA-RT15HT, EHV; Features: 15 Deg Compression terminal for 250 Deg C ACSS transmission lines at 345 kV and over; For ACSS Conductor; RoHS Under Investigation; Conductor Range (Main/Primary): 556.5 KCMIL ACSS.



### Product Details

#### General

Connector Type	Terminal
UPC	781810493458
UPC 12 Digit	7818104934588

#### Dimensions

Dimension - D inch	4.50 in
Dimension - Length Overall inch	17.12 in
Dimension - Pad Width inch	3.25 in

#### Conductor Related

Conductor - ACSS Str Size	556.5 (24/7) kcmil;556.5 (26/7)kcmil
Conductor - ACSS Str Size Range	556.5 (24/7) kcmil-556.5 (26/7)kcmil

#### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)