

# BYNA451R15HT

by Burndy  
Catalog ID: BYNA451R15HT

Prop 65 Notice

BURNDY; HYLUG; BYNA-R15HT; Features: 15 Deg Compression terminal for ACSS transmission lines up to and including 230 kV; For ACSS Conductor; RoHS Under Investigation.



## Product Details

### General

Connector Type	Terminal
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	781810497432
UPC 12 Digit	7818104974322

### Dimensions

Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	14/25
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	15.10 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Pad Width inch	3.22 in

### Conductor Related

Conductor - ACSS Str Size	715.5 (24/7) kcmil;715.5 (26/7) kcmil;715.5 (30/19) kcmil;795 (42/7) kcmil;795 (20/7) kcmil;795 (45/7) kcmil;795 (22/7) kcmil;795 (24/7) kcmil;795 (54/7) kcmil;795 (26/7) kcmil;795 (30/19) kcmil
Conductor - ACSS Str Size Range	715.5 (24/7) kcmil-795 (30/19) kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)