

BYNA451RT15ACCC

by Burndy
Catalog ID: BYNA451RT15ACCC

HYLUG™ Terminal Pad Assembly (ACCC), 540mm² ACCC, 15°, 230kV



Product Details

General

| | |
|---------------------------------------|---------------|
| Connector Type | Terminal |
| Die Index | 725 |
| Feature - Barrel Style | Tapered |
| Installation Torque Recommended in-lb | 300 in-lb |
| Material | Aluminum |
| Physical Attribute - Number of Holes | 4 |
| Trade Name | HYLUG™ |
| UPC | 781810514375 |
| UPC 12 Digit | 7818105143755 |

Dimensions

| | |
|---|-----------|
| Dimension - Bolt Size fraction | 1/2 |
| Dimension - D inch | 3.95 in |
| Dimension - F Width Center to Center inch | 1.75 in |
| Dimension - Hole Size inch | 0.56 in |
| Dimension - Inside Diameter inch | 1.18 in |
| Dimension - L Length Overall mm | 381 mm |
| Dimension - Length Overall inch | 15 in |
| Dimension - N inch | 0.63 in |
| Dimension - Outside Diameter inch | 1.8 in |
| Dimension - Pad Width inch | 3.22 in |
| Dimension - Thread Size | 1/2 |
| Physical Attribute - Tongue Angle | 15 Degree |

Conductor Related

| | |
|---------------------------------|----------------|
| Conductor - ACCC Str Size | 540mm²(Dublin) |
| Conductor - ACCC Str Size Range | 540mm²(Dublin) |

Certifications and Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)