

# BYNA451RTHT

by Burndy  
Catalog ID: BYNA451RTHT

Prop 65 Notice

BURNDY; HYLUG; BYNA-RTHT, EHV; Features: Straight Compression terminal for 250 DegC ACSS transmission lines at 345 kV and over; For ACSS Conductor; RoHS Under Investigation.



## Product Details

### General

Connector Type	Terminal
Feature - Barrel Style	Tapered
Feature - Barrel Type	Long
Material	Aluminum
Physical Attribute - Number of Holes	4
UPC	781810514399
UPC 12 Digit	7818105143999

### Dimensions

Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	15.46 in
Dimension - N inch	1.12 in
Dimension - Outside Diameter inch	1.8 in
Dimension - Pad Width inch	3.22 in
Dimension - Thread Size	1/2
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - ACSS Str Size	715.5 (26/7) kcmil
Conductor - ACSS Str Size Range	715.5 (26/7) kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)