

BYNA49R15HHT

by Burndy
 Catalog ID: BYNA49R15HHT

Prop 65 Notice

BURNDY; HYLUG; BYNA-R-HHT, Kit; Features: Single pad Full tension compression deadend for 250 Deg C rated ACSS transmission lines up to and including 230kV; Standard 15 Deg NEMA tap pad provides either 0 Deg or 30 Deg tap when BYNA-R15 terminal is used; with Hardware; For ACSS Conductor; RoHS Compatible.



Product Details

General

Connector Type	Terminal
Trade Name	HYLUG™
UPC	781810495810
UPC 12 Digit	7818104958100

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)