

BYNA52RT15HT

by Burndy
Catalog ID: BYNA52RT15HT

BURNDY; HYLUG; BYNA-RT15HT, EHV; Features: 15 Deg Compression terminal for 250 Deg C ACSS transmission lines at 345 kV and over; For ACSS Conductor; RoHS Under Investigation; Conductor Range (Main/Primary): 1113 (54-19 Str) - 1351.5 KCMIL ACSS.



Product Details

General

Connector Type	Splice
UPC	781810490860
UPC 12 Digit	7818104908600

Dimensions

Dimension - D inch	3.95 in
Dimension - Length Overall inch	16.81 in
Dimension - Pad Width inch	3.22 in

Conductor Related

Conductor - ACSS Str Size	1113 (54/19)kcmil;1192.5 (45/7)kcmil;1272 (45/7)kcmil;1272(54/19)kcmil;1351.5(45/7)kcmil;1351.5(54/19)kcmil
Conductor - ACSS Str Size Range	1113 (54/19)kcmil-1351.5(54/19)kcmil

Certifications and Compliance

Standards - RoHS Compliance Status	UI
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)