

## BYNA56R15HHT

by Burndy

Catalog ID: BYNA56R15HHT

Prop 65 Notice

BURNDY; HYLUG; BYNA-R-HHT, Kit; Features: Single pad Full tension compression deadend for 250 Deg C rated ACSS transmission lines up to and including 230kV; Standard 15 Deg NEMA tap pad provides either 0 Deg or 30 Deg tap when BYNA-R15 terminal is used; with Hardware; For ACSS Conductor; RoHS Under Investigation.



## Product Details

### General

|                |               |
|----------------|---------------|
| Connector Type | Terminal      |
| UPC            | 781810511909  |
| UPC 12 Digit   | 7818105119099 |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Standards - RoHS Compliance Status | UI |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)