

BYNA590MRT15HACCC

by Burndy
Catalog ID: BYNA590MRT15HACCC

Prop 65 Notice

HYLUG™ TERMINAL With Hardware Kit TMH24, CTC NO. 600-253-6,
Accommodates HAMBURG 570/MILAN 590/ROME 610 ACCC® BURNDY,
DIE 727,15 Degree, OVER-LAP CRIMPS



Product Details

General

Application	For ACCC Conductor, Corona free operation up to 230 KV
Connector Type	Terminal
Die Index	727
Die Type	L727W
Feature - Barrel Style	Tapered
Installation Torque Recommended in-lb	300 in-lb
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	15 Degree
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810487709
UPC 12 Digit	7818104877099

Dimensions

Dimension - D inch	3.95 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Height inch	3.92 in
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	15.7 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.97 in
Dimension - Pad Width inch	3.22 in
Weight	3.1 lb

Electrical Ratings

Voltage - Maximum	230 kV
-------------------	--------

Conductor Related

Conductor - ACCC Str Size	HAMBURG 570 mm ² , MILAN 590 mm ² , ROME 610 mm ²
Conductor - Material	Aluminum

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)