

BYNA59R15HT

by Burndy
Catalog ID: BYNA59R15HT

HYLUG™ Terminal Pad Assembly (ACCC), 2156 kcmil-2167 kcmil ACSS



Product Details

General

Connector Type	Terminal
Die Index	735
Installation Torque Recommended in-lb	300 in-lb
Trade Name	HYLUG™
UPC	781810487235
UPC 12 Digit	7818104872355

Dimensions

Dimension - D inch	3.95 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	456 mm
Dimension - Length Overall inch	17.95 in
Dimension - Outside Diameter inch	2.50 in
Dimension - Pad Width inch	3.57 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - ACSS Str Size	2156 kcmil-2167 kcmil
Conductor - ACSS Str Size Range	2156(84/19) kcmil-2167(72/7) kcmil

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)