

## BYNS43RHT

by Burndy  
Catalog ID: BYNS43RHT

Jumper Loop sleeve for 250 Deg C ACSS transmission lines at 230 kV and over; Sleeve is pre-filled with PENETROX joint compound and capped; For ACSS Conductor; RoHS Under Investigation



### Product Details

#### General

Connector Type	Tap
Die Index	724
UPC	781810510964
UPC 12 Digit	7818105109644

#### Dimensions

Dimension - Length Overall inch	19.74 in
Dimension - Outside Diameter inch	1.61 in

#### Conductor Related

Conductor - ACSS Str Size	605 (24/7) kcmil;605 (26/7) kcmil;636 (24/7) kcmil;636 (26/7) kcmil;666.6 (24/7) kcmil
Conductor - ACSS Str Size Range	605 (24/7) kcmil-666.6 (24/7) kcmil

#### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)