

# BYNS451RHT

by Burndy  
Catalog ID: BYNS451RHT

BURNDY; SLEEVE; BYNS-RHT; Features: Jumper Loop sleeve for 250 Deg C ACSS transmission lines at 230 kV and over; Sleeve is pre-filled with PENETROX joint compound and capped; Overall Length: 18.60 IN; For ACSS Conductor; RoHS Under Investigation



## Product Details

### General

Connector Type	Splice
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810497456
UPC 12 Digit	7818104974566

### Dimensions

Dimension - L Length Overall mm	472 mm
Dimension - Length Overall inch	18.60 in

### Conductor Related

Conductor - ACSR Cmpt Size	8 AWG
Conductor - ACSR Cmpt Size Range	8 AWG
Conductor - ACSR Str Size	6 (6/1) Turkey AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG
Conductor - ACSS Str Size	715.5 (26/7) kcmil;715.5 (30/19) kcmil;795 (42/7) kcmil;795 (20/7) kcmil;795 (45/7) kcmil;795 (22/7) kcmil;795 (24/7) kcmil;795 (54/7) kcmil
Conductor - ACSS Str Size Range	715.5 (26/7) kcmil-795 (54/7) kcmil
Conductor - AL Str Size	12 AWG
Conductor - AL Str Size Range	12 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)