

## BYNS49RHT

by Burndy  
Catalog ID: BYNS49RHT

BURNDY; SLEEVE; BYNS-RHT; Features: Jumper Loop sleeve for 250 Deg C ACSS transmission lines at 230 kV and over; Sleeve is pre-filled with PENETROX joint compound and capped; For ACSS Conductor; RoHS Under Investigation



### Product Details

#### General

Connector Type	Splice
UPC	781810507186
UPC 12 Digit	7818105071866

#### Dimensions

Dimension - Length Overall inch	18.70 in
---------------------------------	----------

#### Conductor Related

Conductor - ACSS Str Size	900 (45/7) kcmil;900 (54/7) kcmil;954 (42/7) kcmil;954 (20/7) kcmil;954 (45/7) kcmil;954 (48/7) kcmil;954 (24/7) kcmil;954 (54/7) kcmil;954 (30/19) kcmil;1033.5 (42/7) kcmil;1033.5 (45/7) kcmil;1033.5 (48/7) kcmil;1033.5 (54/7) kcmil;1113 (42/7) kcmil;1113 (45/7) kcmil
Conductor - ACSS Str Size Range	900 (45/7) kcmil-1113 (45/7) kcmil

#### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	UI

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)