



C11B

by Burndy
Catalog ID: C11B

Prop 65 Notice

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1/2"- 1" Water Pipe.

Features: For Connecting Grounding Conductor To Water Pipe Or Copper Tube, B Indicates Brass Hardware, Water Pipe Size: 3/8 - 1 IN, Installation Torque: 50 IN-LB For Pipe And Wire Clamp, Cross Flats: 0.63 IN, Length: 2.25 IN, Width: 0.63 IN, Height: 1.81 IN, Armored Cable: No, Ground Strap: No

Product Details

General

Application	For Bare Wire, Connecting Grounding Conductor To Water Pipe Or Copper Tube
Material	Bronze Alloy
Material - Hardware	Brass
Plated	Y
Plating Type	Zinc Plated
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810142363
UPC 12 Digit	7818101423633

Dimensions

Dimension - Height inch	1.81 in
Dimension - Hole Size inch	0.31 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	57 mm
Dimension - Length Overall inch	2.25 in
Dimension - Pad Width inch	0.63 in
Dimension - Width inch	0.63 in
Dimension - Width mm	16 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG-2 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)