

C11CSLH12

by Burndy
Catalog ID: C11CSLH12

Prop 65 Notice

Cast Bronze Ground Clamp w/Cu Strap, 1/2"-1" Water Pipe, #4-#6 Rebar(Main), 1/2" Hub, 2/0-#10 Ground, Zinc Plated H/W



Product Details

General

Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Zinc
UPC	781810358658
UPC 12 Digit	7818103586588

Dimensions

Dimension - D inch	6.12 in
Dimension - Height inch	1.75 in
Dimension - L Length Overall mm	216 mm
Dimension - Length Overall inch	8.50 in
Dimension - Pad Width inch	1.06 in
Dimension - Width inch	1.18 in
Dimension - Width mm	30 mm

Conductor Related

Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Str Size Range	10 AWG-2/0 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)