



C11HD4/0DBRK

by Burndy
Catalog ID: C11HD4/0DBRK

Cast Bronze Body Ground Clamp, Conductor range tap ground: #8 - 4/0 AWG.

Features: For Connecting Grounding Conductor, EMT Or Rigid Conduit To Water Pipe, Copper Tube, Ground Rod Or Rebar, Hub Swings 360 DEG For Easy Alignment, Simply Reverse Bottom Clamp For Smaller Size Rebar Or Rod, Connectors Are Provided With Silicon Bronze Hardware, Installation Torque: 50 IN-LB For Screw, Length: 2.65 IN, Height: 2.25 IN, Ground Rod Size: 3/8 - 1 IN Outer-Diameter, Rebar Size: #4 - #6, Package: Clamshell, Water Pipe Size: 1/2 - 1 IN, Width: 1.56 IN

Product Details

General

Application	For Connecting Grounding Conductor, EMT Or Rigid Conduit To Water Pipe, Copper Tube, Ground Rod Or Rebar, Direct Burial Applications
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810359686
UPC 12 Digit	7818103596866

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)