



C11K16DRK

by Burndy
Catalog ID: C11K16DRK

Prop 65 Notice

Cast Bronze Body Ground Clamp, Recommended Screw Torque:50 in.-lbs.

Features: With Lay-in Feature, For Connecting Grounding Conductor To Water Pipe, Copper Tube, Ground Rod Or Rebar, The Open Face Design Allows For Fast Lay-In Of The Tap Conductor Without The Need For Cutting, Simply Reverse Bottom Clamp For Smaller Size Rebar Or Rod, Connectors Are Provided With Silicon Bronze Hardware, Installation Torque: 50 IN-LB For Screw, Ground Rod Size: 3/8 - 1 IN Outer-Diameter, Package: Clamshell, Width: 0.66 IN, Water Pipe Size: 1/2 - 1 IN, Height: 1.64 IN, Length: 2.28 IN, Rebar Size: #4 - #6

Product Details

General

Application	For Connecting Grounding Conductor To Water Pipe, Copper Tube, Ground Rod Or Rebar, Direct Burial Applications
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810359709
UPC 12 Digit	7818103597099

Certifications and Compliance

Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
Number of Pieces in Package	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)