



C11K17D

by Burndy
Catalog ID: C11K17D

Prop 65 Notice

Cast Bronze Ground Clamp w/Lay-in Feature, 1/2"-1" Water Pipe, #4-#6 Rebar, 3/8"-1" Ground Rod(Main), #10 Sol-#2 Str Ground, Silicon Bronze H/W.

Features: For Connecting Grounding Conductor To Water Pipe, Copper Tube, Ground Rod Or Rebar, The Open Face Design Allows For Fast Lay-In Of The Tap Conductor Without The Need For Cutting, Simply Reverse Bottom Clamp For Smaller Size Rebar Or Rod, Connectors Are Provided With Silicon Bronze Hardware, With Lay-In Feature, Water Pipe Size: 1/2 - 1 IN, Height: 1.64 IN, Rebar Size: #4 - #6, Ground Rod Size: 3/8 - 1 IN, Length: 2.28 IN, Width: 0.66 IN, Installation Torque: 50 IN-LB

Product Details

General

Application	For Connecting Grounding Conductor To Water Pipe, Copper Tube, Ground Rod Or Rebar And Direct Burial
Construction Material - Main	Cast Bronze Body
Material	Copper
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810358634
UPC 12 Digit	7818103586344

Dimensions

Dimension - Height inch	1.64 in
Dimension - L Length Overall mm	58 mm
Dimension - Length Overall inch	2.28 in
Dimension - Width inch	0.66 in
Dimension - Width mm	17 mm

Conductor Related

Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG-2 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in
Conductor - Rebar Size	4 ;5 ;6
Conductor - Rebar Size Range	4 -6
Conductor - Rod Size	3/8 in;1/2 in;5/8 in;3/4 in;7/8 in;1 in
Conductor - Rod Size Range	3/8 in-1 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)