



C11LH1

by Burndy
Catalog ID: C11LH1

Prop 65 Notice

Cast Bronze Clamp, Cable to Water Pipe, 10 AWG -6 AWG, 1/2" - 1" Water Pipe, 1/2" hub.

Features: For Grounding Rigid Conduit Systems, Continuity From Rigid Conduit Systems To Ground Provided By Cast Bronze Threaded Conduit Hub, Zinc Plated Screws, Ground Strap: No, Dimension C: 0.97 IN, Armored Cable: No, Water Pipe Size: 3/8 - 1 IN, Installation Torque: 50 IN-LB For Pipe Clamp And Wire Clamp, Hub Size: 1/2 IN, Width: 0.69 IN, Length: 3.23 IN, Height: 2.25 IN

Product Details

General

Application	For Grounding Rigid Conduit Systems
Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Unplated
Sub Brand	CONDUIT
Type	WaterPipe Gounding Connectors
UPC	781810142141
UPC 12 Digit	7818101421411

Dimensions

Dimension - Height inch	2.25 in
Dimension - L Length Overall mm	82 mm
Dimension - Length Overall inch	3.23 in
Dimension - Pad Width inch	0.97 in
Dimension - Width inch	0.69 in
Dimension - Width mm	18 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG
Conductor - Copper Solid Size Range	10 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Size Range	10 AWG-6 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)