



C22DRK

by Burndy
Catalog ID: C22DRK

Prop 65 Notice

Cast Bronze Body Ground Clamp, Conductor Range (Main/Primary): 10 - 2 AWG Stranded, Length: 3.63 IN, Installation Torque: 50 IN-LB For Pipe.

Features: For Connecting Grounding Conductor To Water Pipe Or Copper Tube, D Indicates UL467 Listed For Direct Burial In Earth And Concrete And Are Supplied With Silicon Bronze Hardware, Length: 3.63 IN, Width: 0.75 IN, Cross Flats: 1 IN, Dimension C: 1 IN, Height: 2.38 IN, Installation Torque: 50 IN-LB For Pipe And Wire Clamp, Armored Cable: No, Ground Strap: No, Water Pipe Size: 1-1/4 - 2 IN, Package: Clamshell

Product Details

General

Application	For Connecting Grounding Conductor To Water Pipe Or Copper Tube, Direct Burial Applications In Earth And Concrete
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810359730
UPC 12 Digit	7818103597300

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)