



## C22D

by Burndy  
Catalog ID: C22D

Prop 65 Notice

Cast Bronze Ground Clamp, Cable to Water Pipe or Copper Tube, 10 - 2 AWG, 1-1/4" - 2" Water Pipe.

Features: For Connecting Grounding Conductor To Water Pipe Or Copper Tube, D Indicates UL467 Listed For Direct Burial In Earth And Concrete And Are Supplied With Silicon Bronze Hardware, Water Pipe Size: 1-1/4 - 2 IN, Installation Torque: 50 IN-LB For Pipe And Wire Clamp, Length: 3.63 IN, Cross Flats: 1 IN, Width: 0.75 IN, Height: 2.38 IN, Armored Cable: No, Ground Strap: No

## Product Details

### General

Application	For Connecting Grounding Conductor To Water Pipe Or Copper Tube, Direct Burial Applications In Earth And Concrete
Material	Bronze Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Sub Brand	CLAMP
Type	Ground Clamp
UPC	781810142356
UPC 12 Digit	7818101423566

### Dimensions

Dimension - Height inch	2.38 in
Dimension - Hole Size inch	0.31 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	92 mm
Dimension - Length Overall inch	3.63 in
Dimension - Pad Width inch	1.00 in
Dimension - Width inch	0.75 in
Dimension - Width mm	19 mm

### Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Solid Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	10 AWG-2 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG-2 AWG
Conductor - Pipe EMT Size	1 1/4 in;1 1/2 in;2 in
Conductor - Pipe EMT Size Range	1 1/4 in-2 in

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)