



C6

by Burndy
Catalog ID: C6

Prop 65 Notice

Cast Bronze Clamp, Armored Cable to Water Pipe, 10 AWG - 2 AWG (Str.), 1/2" - 1" Water Pipe, pipe clamp: 50 in-lb.

Features: For Connecting Armored Cable To Water Pipe, Zinc Plated Screws, Supplied With Silicon Bronze Hardware, Armored Cable: Yes, Ground Strap: No, Dimension C: 0.63 IN, Installation Torque: 50 IN-LB For Pipe Clamp And Wire Clamp, Length: 2.34 IN, Height: 1.6 IN, Width: 16 IN, Water Pipe Size: 3/8 - 1 IN

Product Details

General

Application	For Connecting Armored Cable To Water Pipe
Hardware Type	Zinc Plated
Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	Y
Plating Type	Zinc
Sub Brand	CLAMP
Trade Name	N
Type	Ground Clamp
UPC	781810142394
UPC 12 Digit	7818101423944

Dimensions

Dimension - Height inch	1.60 in
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.34 in
Dimension - Pad Width inch	0.63 in
Dimension - Thread Size	-
Dimension - Width inch	1.06 in
Dimension - Width mm	27 mm

Conductor Related

Conductor - Armored Cable Size	Y
Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	10 AWG-2 AWG
Conductor - Pipe EMT Size	3/8 in;1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	3/8 in-1 in

Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size • Pipe EMT-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	N
Certification - cULus	N
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)